



Magnetic Stirrer with Heating



Product Highlights

- Fast temperature ramping saves time
- Speed and temperature LED Display
- Hotplate safety warning light
- Chemically-resistant ceramic-coated plate
- Includes 40mm stir bar
- 2-year warranty

Product Applications

Stirring

Mixing

Heating

Buffer preparation

Dissolving elements and compounds

Cultivating microbial life

Prevent settling and caking in liquids

STARLAB reserves the right to make changes at any time and without prior notice. The content and design of this PDF are protected by national and international copyright law and are the property of STARLAB International GmbH. Any duplication, editing, distribution and any kind of use and utilization of this PDF content in electronic systems, online media and / or libraries or similar databases requires the prior consent of STARLAB International GmbH.

Starlab (UK) LTD
5 Tanners Drive
MK14 5BU Milton Keynes
Email: infoline@starlab.co.uk



General Data

Art. No.	N2400-3010
Dimensions (W × D × H)	155 mm × 215 mm × 75 mm
Dimensions (W × D)	155 mm × 215 mm
Plate Diameter	135 mm
Weight	1.4 kg
Max. stirring volume	3 l
Pack Size	1 Piece (1 Box × 1 Piece)
Power supply	200 – 240 V, 50/60 Hz
Max. temp.	40 °C
Permissible Ambient Temperature	Ambient to 280 °C with 1 °C increments
Temperature range	4 to 40 °C
Temperature min. (SL)	4 °C
Max. RCF	1500 rpm
Speed Range	100 – 1,500 rpm

STARLAB reserves the right to make changes at any time and without prior notice. The content and design of this PDF are protected by national and international copyright law and are the property of STARLAB International GmbH. Any duplication, editing, distribution and any kind of use and utilization of this PDF content in electronic systems, online media and / or libraries or similar databases requires the prior consent of STARLAB International GmbH.

Starlab (UK) LTD
5 Tanners Drive
MK14 5BU Milton Keynes
Email: infoline@starlab.co.uk



More informations about Magnetic Stirrer with Heating

Stir up some heat!

This magnetic stirrer has very fast temperature ramping to help save your time. The ceramic-coated plate ensures an even temperature and has a high resistance to chemicals. It is ideal for many applications including the preparation of solvents at high temperatures. Supplied with a 40 mm magnetic stir bar, the stirrer is easy to use and has a clear LED display showing temperature and speed.

STARLAB reserves the right to make changes at any time and without prior notice. The content and design of this PDF are protected by national and international copyright law and are the property of STARLAB International GmbH. Any duplication, editing, distribution and any kind of use and utilization of this PDF content in electronic systems, online media and / or libraries or similar databases requires the prior consent of STARLAB International GmbH.

Starlab (UK) LTD
5 Tanners Drive
MK14 5BU Milton Keynes
Email: infoline@starlab.co.uk



Accessories

PRODUCT NAME	PACKAGING SIZE	ART. NO.
 Temperature sensor PT1000	1 Piece (1 Box × 1 Piece)	N2400-3011

STARLAB reserves the right to make changes at any time and without prior notice. The content and design of this PDF are protected by national and international copyright law and are the property of STARLAB International GmbH. Any duplication, editing, distribution and any kind of use and utilization of this PDF content in electronic systems, online media and / or libraries or similar databases requires the prior consent of STARLAB International GmbH.

Starlab (UK) LTD
5 Tanners Drive
MK14 5BU Milton Keynes
Email: infoline@starlab.co.uk