




Metal Block for 12 x 15ml Centrifuge Tube



Product Highlights

- Well diameter: 17.3 mm
- Well depth: 45 mm
- For use with N2400-4001 and N2400-4002
- Supplied with screw in handle for insertion/removal

Product Applications

STARLAB reserves the right to make changes at any time and without prior notice. The content and design of this PDF are protected by national and international copyright law and are the property of STARLAB International GmbH. Any duplication, editing, distribution and any kind of use and utilization of this PDF content in electronic systems, online media and / or libraries or similar databases requires the prior consent of STARLAB International GmbH.

Starlab (UK) LTD
5 Tanners Drive
MK14 5BU Milton Keynes
Email: info@starlab.co.uk



General Data

| | |
|------------------------|------------------------------------|
| Art. No. | N2400-4102 |
| Pack Size | 1 Piece (1 Box × 1 Piece) |
| Dimensions (W × D × H) | 80 mm × 105 mm × 50 mm |
| Dimensions (W × D) | 80 mm × 105 mm |
| Well diameter | 17.30 mm |
| Well depth | 45.0 mm |
| System | Dry Bath Incubator (Single & Dual) |
| For use with | 12 x 15 ml centrifuge tubes |

STARLAB reserves the right to make changes at any time and without prior notice. The content and design of this PDF are protected by national and international copyright law and are the property of STARLAB International GmbH. Any duplication, editing, distribution and any kind of use and utilization of this PDF content in electronic systems, online media and / or libraries or similar databases requires the prior consent of STARLAB International GmbH.

Starlab (UK) LTD
5 Tanners Drive
MK14 5BU Milton Keynes
Email: info@starlab.co.uk



More informations about Metal Block for 12 x 15ml Centrifuge Tube

Metal block for use with the single block (N2400-4001) or dual block (N2400-4002) Dry Bath Systems.

The single & dual block dry bath is designed for a wide variety of applications. Additional function of a water bath.

Available as single or dual block units, these systems offer great value and convenience for the user. A range of **metal blocks** are available below.