




## Metal Block for 96-Well PCR Plates (Single)



### Product Highlights

- Well diameter: 6.28 mm
- Well depth: 15mm
- For use with N2400-4001 only
- Supplied with screw in handle for insertion/removal

## Product Applications

STARLAB reserves the right to make changes at any time and without prior notice. The content and design of this PDF are protected by national and international copyright law and are the property of STARLAB International GmbH. Any duplication, editing, distribution and any kind of use and utilization of this PDF content in electronic systems, online media and / or libraries or similar databases requires the prior consent of STARLAB International GmbH.

**Starlab (UK) LTD**  
5 Tanners Drive  
MK14 5BU Milton Keynes  
Email: [infoline@starlab.co.uk](mailto:infoline@starlab.co.uk)



## General Data

Art. No.	N2400-4107
Dimensions (W × D × H)	87 mm × 128 mm × 70 mm
Dimensions (W × D)	87 mm × 128 mm
Well diameter	6.28 mm
Well depth	15.0 mm
Pack Size	1 Piece (1 Box × 1 Piece)
System	Dry Bath Incubator (Single & Dual)
For use with (SL)	96-well PCR plate (Single Block only)

STARLAB reserves the right to make changes at any time and without prior notice. The content and design of this PDF are protected by national and international copyright law and are the property of STARLAB International GmbH. Any duplication, editing, distribution and any kind of use and utilization of this PDF content in electronic systems, online media and / or libraries or similar databases requires the prior consent of STARLAB International GmbH.

**Starlab (UK) LTD**  
5 Tanners Drive  
MK14 5BU Milton Keynes  
Email: [infoline@starlab.co.uk](mailto:infoline@starlab.co.uk)



## More informations about Metal Block for 96-Well PCR Plates (Single)

Metal block for use with the single block (N2400-4001) Dry Bath System.

The single & dual block dry bath is designed for a wide variety of applications. Additional function of a water bath.

Available as single or dual block units, these systems offer great value and convenience for the user. A range of **metal blocks** are available below.