



## Magnetic Stirrer with Heating



### Product Highlights

- Fast temperature ramping saves time
- Speed and temperature LED Display
- Hotplate safety warning light
- Chemically-resistant ceramic-coated plate
- Includes 40mm stir bar
- 2-year warranty

## Product Applications

Stirring

Mixing

Heating

Buffer preparation

Dissolving elements and compounds

Cultivating microbial life

Prevent settling and caking in liquids

STARLAB reserves the right to make changes at any time and without prior notice. The content and design of this PDF are protected by national and international copyright law and are the property of STARLAB International GmbH. Any duplication, editing, distribution and any kind of use and utilization of this PDF content in electronic systems, online media and / or libraries or similar databases requires the prior consent of STARLAB International GmbH.

**Starlab International GmbH**  
Neuer Höltigbaum 38  
22143 Hamburg  
Email: [info@starlab.de](mailto:info@starlab.de)



## General Data

|                                 |  |
|---------------------------------|--|
| Art. No.                        | N2400-3010                             |
| Dimensions (W × D × H)          | 155 mm × 215 mm × 75 mm                |
| Dimensions (W × D)              | 155 mm × 215 mm                        |
| Plate Diameter                  | 135 mm                                 |
| Weight                          | 1.4 kg                                 |
| Max. stirring volume            | 3 l                                    |
| Pack Size                       | 1 Piece (1 Box × 1 Piece)              |
| Power supply                    | 200 – 240 V, 50/60 Hz                  |
| Max. temp.                      | 40 °C                                  |
| Permissible Ambient Temperature | Ambient to 280 °C with 1 °C increments |
| Temperature range               | 4 to 40 °C                             |
| Temperature min. (SL)           | 4 °C                                   |
| Max. RCF                        | 1500 rpm                               |
| Speed Range                     | 100 – 1,500 rpm                        |

STARLAB reserves the right to make changes at any time and without prior notice. The content and design of this PDF are protected by national and international copyright law and are the property of STARLAB International GmbH. Any duplication, editing, distribution and any kind of use and utilization of this PDF content in electronic systems, online media and / or libraries or similar databases requires the prior consent of STARLAB International GmbH.

**Starlab International GmbH**  
Neuer Höltigbaum 38  
22143 Hamburg  
Email: [info@starlab.de](mailto:info@starlab.de)



## More informations about Magnetic Stirrer with Heating

### **Stir up some heat!**

This magnetic stirrer has very fast temperature ramping to help save your time. The ceramic-coated plate ensures an even temperature and has a high resistance to chemicals. It is ideal for many applications including the preparation of solvents at high temperatures. Supplied with a 40 mm magnetic stir bar, the stirrer is easy to use and has a clear LED display showing temperature and speed.



## Accessories

| PRODUCT NAME  | PACKAGING SIZE            | ART. NO.   |
|---|---------------------------|------------|
|  <a href="#">Temperature sensor PT1000</a> | 1 Piece (1 Box × 1 Piece) | N2400-3011 |

STARLAB reserves the right to make changes at any time and without prior notice. The content and design of this PDF are protected by national and international copyright law and are the property of STARLAB International GmbH. Any duplication, editing, distribution and any kind of use and utilization of this PDF content in electronic systems, online media and / or libraries or similar databases requires the prior consent of STARLAB International GmbH.

**Starlab International GmbH**  
Neuer Höltigbaum 38  
22143 Hamburg  
Email: [info@starlab.de](mailto:info@starlab.de)